


# ONLINE GAS REGULATOR-300



## OverPressurization Protection

*Protect the downstream piping system and the regulator's low pressure chambers against overpressurization due to possible regulator malfunction or failure to achieve complete lockup. The allowable outlet pressure is the lowest of the maximum pressure permitted by federal codes, state codes, NUTECH bulletin NEV - 300, or other applicable standard. The method of protection can be relief valve, monitor regulator, shutoff device, or similar mechanism.*

## TECHNICAL SPECIFICATION

<i>Application</i>	<i>:-</i>	<i>Air/Liquide/Gas</i>
<i>Sizes</i>	<i>:-</i>	<i><math>\frac{1}{2}</math>" , <math>\frac{3}{4}</math>" NPT</i>
<i>Inlet Pressure-Max.</i>	<i>:-</i>	<i>5000 PSIG</i>
<i>Outlet Pressure-Max.</i>	<i>:-</i>	<i>4000 PSIG</i>
<i>Temperature</i>	<i>:-</i>	<i>150° F</i>
<i>Orifice Size</i>	<i>:-</i>	<i><math>\frac{1}{8}</math>" , <math>\frac{1}{4}</math>" , <math>\frac{3}{8}</math>" , <math>\frac{7}{16}</math>" , <math>\frac{1}{2}</math>" , <math>\frac{5}{8}</math>" , <math>\frac{7}{8}</math>"</i>
<i>Pressure</i>	<i>:-</i>	<i>1650* , 1150* , 550 , 450 , 350 , 300 , 200 PSI</i>

### *Nutech Valves*

*37, Shreeji Industrial Estate, Raypur Mill Compound, Saraspur, Ahmedabad - 24*

*Ph..( O ) :- 079 - 29292112, 32923375 Fax :- 079 - 22133122*

*E-Mail :- sales@nutechvalves.com Website :- www.nutechvalves.com*

**AN ISO 9001:2000 Certified Co.**